



FD685T12CG2

by Burndy
Catalog ID: FD685T12CG2

Stud Connector, 2-1/4 IN Stud to 6 Holes NEMA Pad, Material: Cast Copper Alloy

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy, Cast
Material - Hardware	Durium
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	621945010680
UPC 12 Digit	6219450106800

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Length Overall inch	8.62 in
Dimension - Pin Diameter inch	2.25 in
Dimension - Threads per inch	12
Dimension - Width inch	4.00 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)