



## FD68T12CG9

by Burndy  
Catalog ID: FD68T12CG9

Stud Connector, 2 IN Stud to 4 Holes NEMA Pad, Material: Cast Copper Alloy

### Product Details

#### General

Application	Substation
Connector Type	Stud Connector
Installation Torque Recommended in-lb	360 lbs-in
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin Plated
Type	Studs
UPC	621945144569
UPC 12 Digit	6219451445699

#### Dimensions

Dimension - B Length inch	2.69 in
Dimension - Length Overall inch	6.56 in
Dimension - Pin Diameter fraction	2 in
Dimension - Pin Diameter inch	2.00 in
Dimension - Threads per inch	12
Dimension - Width inch	2.88 in

#### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

#### Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)