



FD65T0CG2

by Burndy
Catalog ID: FD65T0CG2

Stud Connector, 1.00 IN Smooth Stud to 4 Holes NEMA, Material: Cast Copper Alloy

Product Details

General

Application	Substation
Connector Type	Stud Connector
Installation Torque Recommended in-lb	360 lbs-in
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin Plated
Type	Studs
UPC	621945144385
UPC 12 Digit	6219451443855

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	2.68 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	167 mm
Dimension - Length Overall inch	6.56 in
Dimension - Pin Diameter fraction	1 in
Dimension - Pin Diameter inch	1.00 in
Dimension - Width inch	2.88 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)