



FDA67T1224TN

by Burndy
Catalog ID: FDA67T1224TN

Copper Stud Connectors

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Pad Orientation	90 Degree - horizontal
Plated	Y
Plating Type	Tin - Electro Plated
Type	Studs
UPC	621945253490
UPC 12 Digit	6219452534900

Dimensions

Dimension - D inch	3.00 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.38 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Pin Diameter inch	1.5 in
Dimension - Threads per inch	12

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)