



FD67D8

by Burndy
Catalog ID: FD67D8

Prop 65 Notice

Cast Copper Alloy Stud Connector, 1-1/2"-12 Stud, 4 Pad holes, 7.3 in Length, Stud to Flat Bar.

Features: High Copper Alloy Stud Connector Allows Bolting Cable And Tubing Terminals To Equipment Studs, Hex Head Captured Bolts Provide One-Wrench Installation, One Pad Contact Surface Is On Centerline Of Stud, Pad Is Finished On Both Sides, All Pads Are Four Hole NEMA Drilled, Installation Torque: 480 IN-LB, Pad Configuration: Straight, Stud Clamping Hardware: 1/2-13, Stud Size: 1-1/2-12

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	STUD CONNECTOR
Type	Studs
UPC	781810003589
UPC 12 Digit	7818100035899

Dimensions

Dimension - B Length fraction	2-9/50 in
Dimension - B Length inch	2.18 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.00 in
Dimension - L Length Overall mm	185 mm
Dimension - Length Overall inch	7.30 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Pin Diameter inch	1.500 in
Dimension - Thread Size	1/2

Electrical Ratings

Amperage Rating	1450 A
Rating - KVA	230 kV

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)