



GCS26

by Burndy
Catalog ID: GCS26

Ground clamp to steel connector, Conductor range from #6 AWG to 2/0 AWG

- cULus for Grounding and Bonding, Direct Burial rated for installation into earth and concrete
- Accepts beam thickness: .125 - .625" (1/8 to 5/8")
- Conductor range from #6 to 2/0
- Versatile, allows parallel or perpendicular conductor orientation
- Stainless steel hardware
- 5/32" Allen cup point screw penetrates coatings on steel
- No special tooling required
- Applicable for use in "extremely volatile environments"

Stainless steel hardware, Versatile! Allows parallel and perpendicular conductor orientation, No special tooling required for installation

Product Details

General

Application	Applicable for use in extremely volatile environments
Installation Torque Recommended in-lb	180 in-lb on hex nut; 100 in-lb on Allen screw
Material	Copper Alloy, Cast
Material - Hardware	Stainless Steel
Sub Brand	THE CONSTRICTOR
Type	GCS
UPC	621945516144

Dimensions

Height	2.70 in
Length	3.00 in
Weight	1.518 lb
Width	1.60 in

Conductor Related

Conductor - Copper Str Size	#6 to 2/0
-----------------------------	-----------

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)