



FD67T1212

by Burndy
Catalog ID: FD67T1212

Copper Stud Connectors

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	621945010475
UPC 12 Digit	6219450104755

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.00 in
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.25 in
Dimension - Pad Width inch	2.00 in
Dimension - Pin Diameter inch	1.500 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)