



## HSB116T6PF26

by Burndy  
Catalog ID: HSB116T6PF26

Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #18 AWG, 600 V, 6.00" L, Flame Retardant, All Black.

Features: Type HS-T-PF Is A Flexible Thin Wall, Flame Retardant Heat Shrink Tubing Made Of Crosslinked Polyolefin, The 2:1 Shrink Ratio Allows For Faster Shrink Recovery, Covering Wire Sizes 18 AWG To 300 KCMIL, Operating Temperatures From -55 To 135 DEG C With A Shrink Temperature Of 120 DEG C, Inner Diameter Expanded: 06 IN Minimum, Nominal Diameter: 1/16 IN, Inner Diameter After Recovery: 03 IN maximum, Conductor Range: 18 AWG, Material: Cross-Linked Polyolefin

## Product Details

### General

Application	For Terminations And Splices
Material	Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810214404

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	260
Minimum Pack Quantity	1
Number of Pieces in Package	26

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)