



HSB12FR

by Burndy
Catalog ID: HSB12FR

PVC Thin Wall Black Heat Shrink Tubing, #1-#4 Code, #4-#6 Flex, 600 V, Fire Retardant.

Features: Type HS-FR Is A Flexible Polyvinyl Chloride Thin-Wall Heat-Shrink, Offering Insulating, Color Identification And Strain Relieving Properties For Terminations And Splices, The 2:1 Shrink Ratio Allows For Faster Shrink Recovery, Covering Wire Sizes: 16 AWG To 1000 KCML, UL Recognized, 105 DEG C, 600V, Operating Temperatures From -20 DEG C To 105 DEG C With A Shrink Temperature Of 135 DEG C, UL 224, VW-1 Rated, Self-Extinguishing Flame Retardant Properties, Multi-Use Tubing: Insulate, Strain Relief, Easy Identification: Available In Wide Range Of Colors, Low Shrink Temperature: Only Requires Common Hot Air Guns To Apply, Meets MIL-M-23053/Z-206C, Inner Diameter Expanded: 0.5 IN, Inner Diameter After Recovery: 0.25 IN, Conductor Range: 4 - 1 AWG (Code), 6 - 4 AWG (Flex), Material: Polyvinyl Chloride

Product Details

General

Application	For Terminations And Splices
Material	PVC (polyvinyl chloride)
Sub Brand	HEAT SHRINK
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810265789

Dimensions

Thickness	0.03
-----------	------

Conductor Related

Conductor Range	#6 AWG to #4 AWG
-----------------	------------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)