



## FD73F16

by Burndy  
Catalog ID: FD73F16

Copper Stud Connectors

### Product Details

#### General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	6
Physical Attribute - Pad Configuration	6x4 - 6 holes
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810444610
UPC 12 Digit	7818104446100

#### Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Size fraction	5/8
Dimension - D inch	4.00 in
Dimension - Pad Width inch	6.00 in
Dimension - Pin Diameter fraction	4-1/2 in
Dimension - Pin Diameter inch	4.500 in
Dimension - Thread Size	5/8-12
Dimension - Threads per inch	12

#### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

#### Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

#### Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)