



HSB200H9PF2

by Burndy
Catalog ID: HSB200H9PF2

Cross-Linked Polyolefin Heat Shrinkable Heavy Wall Tube, 250 - 350 kcmil, 1000 V, Shrink Ratio: 3 : 1.

Features: Type HS-H-PF Is A Heavy Wall, Flame Retardant Heat Shrink Tubing Made Of Cross-Linked Polyolefin, The Shrink Ratio Is 3:1, And The Inside Diameter Is Coated With An Adhesive Sealant To Protect Against Moisture And Corrosion, UL486D Listed For Direct Burial Applications, Accommodates 14 AWG -500 KCMIL Conductors, Operating Temperatures From -55 DEG C To 135 DEG C With A Shrink Temperature Of 120 DEG C, Cut Lengths and 4 Foot Sticks, Inner Diameter Expanded: 2 IN Minimum, Nominal Diameter: 2 IN, Material: Cross-Linked Polyolefin, Inner Diameter After Recovery: 0.75 IN Maximum, Conductor Range: 250 - 350 KCMIL

Product Details

General

Application	For Direct Burial
Material	Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-H-PF, Heavy Wall, Flame Retardant
UPC	781810214862

Conductor Related

Conductor Range	250-500 Kcmil
-----------------	---------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	20
Minimum Pack Quantity	2
Number of Pieces in Package	2

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)