



FDR67B6J38OV

by Burndy
Catalog ID: FDR67B6J38OV

Copper Stud Connectors

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	2x3.25 - 4 holes
Physical Attribute - Pad Orientation	90 Degree - vertical
Plated	N
Plating Type	Unplated
Type	Studs
UPC	621945276086
UPC 12 Digit	6219452760866

Dimensions

Dimension - B Length fraction	2-9/50 in
Dimension - B Length inch	2.18 in
Dimension - D inch	3.25 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.00 in
Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Pin Diameter inch	1.500 in
Dimension - Threads per inch	12

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)