

HSC112FR

by Burndy
Catalog ID: HSC112FR



Heat Shrink Tubing, 1.5" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250-500 Flex, PVC, Flame Retardant, Clear, 600V.

Features: UL 224, VW-1 Rated: Self-Extinguishing Flame Retardant Properties, Clear Tubing: Allows Inspection Of Die Index Embossed And Shiner After Installation Is Complete, Should Any Corrosion Occur It Will Be Visible During Inspection, Low Shrink Temperature: Only Requires Common Hot Air Guns To Apply, Meets Mil-M-23053/Z-206C, Type HSC-FR Is A Flexible Polyvinyl Chloride Clear Heat-Shrink Tubing, Excellent Flame Retardant Properties And A 2:1 Shrink Ratio, The VISI-SHRINK Tubing Enables Inspectors To Read Die Index Embossments On Installed Connectors Easily, UL Recognized, 105 DEG C, 600V, The Operating Temperature From 20 DEG C To 105 DEG C With A Shrink Temperature Of 135 DEG C, Inner Diameter After Recovery: 0.75 IN, Inner Diameter Expanded: 1.5 IN, Conductor Range: 350 - 300 KCMIL Code, 250 - 500 AWG Flex

Product Details

General

Application	Used on UL Recognized TO 600V
Color	Clear
Material	PVC (polyvinyl chloride)
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Fire Retardant
UPC	781810266151

Conductor Related

Conductor Range	250-500 Kcmil
-----------------	---------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)