



HSB110H9PF5

by Burndy
Catalog ID: HSB110H9PF5

Heat Shrink Tubing, 1.1" ID Min.(Exp.), 0.4" ID Max.(Rec.), 1-3/0 AWG, Cross Linked Polyolefin, Heavy Wall, Flame Retardant, Black, 1000V.

Features: Type HS-H-PF Is A Heavy Wall, Flame Retardant Heat Shrink Tubing Made Of Cross-Linked Polyolefin, The Shrink Ratio Is 3:1, And The Inside Diameter Is Coated With An Adhesive Sealant To Protect Against Moisture And Corrosion, UL486D Listed For Direct Burial Applications, Accommodates 14 AWG -500 KCMIL Conductors, Operating Temperatures From -55 DEG C To 135 DEG C With A Shrink Temperature Of 120 DEG C, Cut Lengths and 4 Foot Sticks, Nominal Diameter: 1.1 IN, Inner Diameter Expanded: 1.1 IN Minimum, Inner Diameter After Recovery: 0.4 IN Maximum, Conductor Range: 1 - 3/0 AWG, Material: Cross-Linked Polyolefin

Product Details

General

| | |
|-------------|--------------------------------------|
| Application | For Direct Burial |
| Material | Polyolefin |
| Sub Brand | HEAT SHRINK |
| Type | HS-H-PF, Heavy Wall, Flame Retardant |
| UPC | 781810214831 |

Conductor Related

| | |
|-----------------|--------------------|
| Conductor Range | #1 AWG to #3/0 AWG |
|-----------------|--------------------|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------------|-----|
| Carton Quantity | 125 |
| Minimum Pack Quantity | 1 |
| Number of Pieces in Package | 5 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)