



## HSB12T300PF

by Burndy  
Catalog ID: HSB12T300PF

Prop 65 Notice

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.12" ID Max.(Rec.), 6-2 AWG, Cross Linked Polyolefin, Thin Wall, Flame Retardant, Black, 600V.

Features: Type HS-T-PF Is A Flexible Thin Wall, Flame Retardant Heat Shrink Tubing Made Of Crosslinked Polyolefin, The 2:1 Shrink Ratio Allows For Faster Shrink Recovery, Covering Wire Sizes 18 AWG To 300 KCMIL, Operating Temperatures From -55 To 135 DEG C With A Shrink Temperature Of 120 DEG C, Nominal Diameter: 1/2 IN, Inner Diameter Expanded: 0.5 IN Minimum, Inner Diameter After Recovery: 0.12 IN Maximum, Conductor Range: 6 - 2 AWG, Material: Cross-Linked Polyolefin

## Product Details

### General

Application	For Terminations And Splices
Material	Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810213735

### Conductor Related

Conductor Range	#6 AWG to #2 AWG
-----------------	------------------

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)