



## HSM14T6PF14

by Burndy  
Catalog ID: HSM14T6PF14

Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #10-14 AWG, 600 V, 6.00" L, Flame Retardant, Multiple Colors.

Features: Type HS-T-PF Is A Flexible Thin Wall, Flame Retardant Heat Shrink Tubing Made Of Crosslinked Polyolefin, The 2:1 Shrink Ratio Allows For Faster Shrink Recovery, Covering Wire Sizes: 18 AWG To 300 KCML, Operating Temperatures From -55 To 135 DEG C With A Shrink Temperature Of 120 DEG C, 6 IN Length, Nominal Diameter: 1/4 IN, Inner Diameter Expanded: 0.25 IN Minimum, Inner Diameter After Recovery: 0.12 IN Maximum, Material: Cross-Linked Polyolefin, Conductor Range: 14 - 10 AWG

### Product Details

#### General

Application	For Terminations And Splices
Color	Multiple Colors
Material	Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810214626

#### Conductor Related

Conductor Range	#14 AWG to #10 AWG
-----------------	--------------------

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Carton Quantity	140
Minimum Pack Quantity	10

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)