



## HSB332T48PF

by Burndy  
Catalog ID: HSB332T48PF

Thin Wall Cross-Linked Black Polyolefin Heat Shrink Tubing, #16-18 AWG, 600 V, Flame Retardant.

Features: Type HS-T-PF Is A Flexible Thin Wall, Flame Retardant Heat Shrink Tubing Made Of Crosslinked Polyolefin, The 2:1 Shrink Ratio Allows For Faster Shrink Recovery, Covering Wire Sizes 18 AWG To 300 KCMIL, Operating Temperatures From -55 To 135 DEG C With A Shrink Temperature Of 120 DEG C, Nominal Diameter: 3/32 IN, Inner Diameter Expanded: 09 IN Minimum, Material: Cross-Linked Polyolefin, Conductor Range: 18 - 16 AWG, Inner Diameter After Recovery: 05 IN Maximum

## Product Details

### General

|             |   |
|-------------|---|
| Application | For Terminations And Splices                  |
| Material    | Polyolefin                                    |
| Sub Brand   | HEAT SHRINK                                   |
| Type        | HS-T-PF, Thin Wall, Flexible, Flame Retardant |
| UPC         | 781810212295                                  |

### Conductor Related

|                 |                    |
|-----------------|--------------------|
| Conductor Range | #18 AWG to #16 AWG |
|-----------------|--------------------|

### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | No  |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)