



K11A39U2N

by Burndy
Catalog ID: K11A39U2N

Prop 65 Notice

Aluminum Universal Terminal, 2 Hole, Two: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, NEMA Spacing, 2 Screws, Al/Cu Rated, Tin Plated.

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port

Product Details

General

| | |
|---------------------------------------|--|
| Application | Terminate multiple conductors onto equipment pads, panel boards, or switchgear |
| Connector Type | Terminal |
| Material | Aluminum |
| Material - Hardware | Aluminum |
| Physical Attribute - Number of Holes | 4 |
| Physical Attribute - Number of Screws | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Type | Bolted Lugs & Terminals |
| UPC | 621945455986 |
| UPC 12 Digit | 6219454559866 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height fraction | 3 in |
| Dimension - Height inch | 3.00 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - Hole Size mm | 14 mm |
| Dimension - L Length Overall mm | 144 mm |
| Dimension - Length Overall inch | 5.69 in |
| Dimension - Screw Size inch | 15/16 |
| Dimension - Stud Size fraction | 3/8 |
| Dimension - Width inch | 1.50 in |
| Dimension - Width mm | 38 mm |

| | |
|-----------|---------|
| Height | 3.00 in |
| Length | 5.34 in |
| Thickness | 0.50 in |
| Width | 1.50 in |

Electrical Ratings

| | |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Conductor Related

| | |
|-------------------------------------|---|
| Conductor - AL Str Size | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil |
| Conductor - AL Str Size Range | 1/0 AWG-750 kcmil |
| Conductor - Copper Solid Size | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Size Range | 1/0 AWG-4/0 AWG |
| Conductor - Copper Str Size | 1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil |
| Conductor - Copper Str Size Range | 1/0 -750 kcmil |
| Conductor Range | 750 Kcmil - #1/0 AWG |
| Conductor Type | <ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Solid-Size |
| Number Of Conductors | 2 |

Certifications and Compliance

| | |
|---|--------------|
| Certification - CSA Approved | Yes |
| Certification - UL Listed Direct Burial | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 50 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)