



HSB35H48PF5

by Burndy
Catalog ID: HSB35H48PF5

Heat Shrink Tubing, 0.35" ID Min.(Exp.), 0.35" ID Max.(Rec.), 14-10 AWG, Cross Linked Polyolefin, Heavy Wall, Flame Retardant, Black, 1000V.

Features: Type HS-H-PF Is A Heavy Wall, Flame Retardant Heat Shrink Tubing Made Of Cross-Linked Polyolefin, The Shrink Ratio Is 3:1, And The Inside Diameter Is Coated With An Adhesive Sealant To Protect Against Moisture And Corrosion, UL486D Listed For Direct Burial Applications, Accommodates 14 AWG -500 KCMIL Conductors, Operating Temperatures From -55 DEG C To 135 DEG C With A Shrink Temperature Of 120 DEG C, Cut Lengths and 4 Foot Sticks, Inner Diameter Expanded: 0.35 IN Minimum, Nominal Diameter: 0.35 IN, Conductor Range: 14 - 10 AWG, Material: Cross-Linked Polyolefin, Inner Diameter After Recovery: 0.15 IN Maximum

Product Details

General

Application	For Direct Burial
Material	Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-H-PF, Heavy Wall, Flame Retardant
UPC	781810214886

Conductor Related

Conductor Range	#14 AWG to #10 AWG
-----------------	--------------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	5

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)