

K22A39U2N

by Burndy
Catalog ID: K22A39U2N

Prop 65 Notice

Aluminum Universal Terminal, 2 Hole, 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing), tin plated

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port



Product Details

General

Application	Terminate multiple conductors onto equipment pads, panel boards, or switchgear
Connector Type	Terminal
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810670163
UPC 12 Digit	7818106701633

Dimensions

Dimension - Hole Size mm	0 mm
Dimension - L Length Overall mm	0 mm
Dimension - Thread Size	-
Dimension - Width mm	0 mm
Height	3.00 in
Length	5.34 in
Width	2.75 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)