



## K2A40U2N

by Burndy  
Catalog ID: K2A40U2N

Prop 65 Notice

Aluminum Universal Terminal, 2 Conductor, 2 Hole, 300-800 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 2 Screws, Al/Cu Rated, Tin Plated.

Universal terminal, Dual-rated two conductor lugs are constructed from high strength aluminum alloy and electro tin-plated to provide low contact resistance

## Product Details

### General

Application	For Aluminum and Copper Conductors
Connector Type	Terminal
Hardware Type	3/8 UNC Slotted Set Screw
Installation Torque Recommended in-lb	375 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810600405
UPC 12 Digit	7818106004055

### Dimensions

Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.03 in
Dimension - Height fraction	2 in
Dimension - Height inch	1.95 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	121 mm
Dimension - Length Overall inch	4.75 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.20 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	1/2 in

Dimension - Width fraction	3-19/100 in
Dimension - Width inch	3.20 in
Dimension - Width mm	81 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - AL Str Size	300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	300-800 kcmil
Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	300-800 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>
Number Of Conductors	2

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
Pallet Quantity	30 EA

**For further technical assistance, please contact us**

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)