

HSC12FR

by Burndy
Catalog ID: HSC12FR



Vinyl Fire Retardant Clear Heat Shrink Tubing, #4-#1(Code) #6-#4(Flex), 600V.

Features: Type HSC-FR Is A Flexible Polyvinyl Chloride Clear Heat-Shrink Tubing, Excellent Flame Retardant Properties And A 2:1 Shrink Ratio, The VISI-SHRINK Tubing Enables Inspectors To Read Die Index Embossments On Installed Connectors Easily, UL Recognized, 105 DEG C, 600V, The Operating Temperature From -20 To 105 DEG C With A Shrink Temperature Of 135 DEG C, UL 224, VW-1 Rated, Self-Extinguishing Flame Retardant Properties, Clear Tubing, Allows Inspection Of Die Index Embossed And Shiner After Installation Is Complete, Should Any Corrosion Occur It Will Be Visible During Inspection, Low Shrink Temperature, Only Requires Common Hot Air Guns To Apply, Meets MIL-M-23053/Z-206C, Inner Diameter After Recovery: 0.25 IN, Inner Diameter Expanded: 0.5 IN, Material: Polyvinyl Chloride, Conductor Range: 4 - 1 AWG (Code), 6 - 4 AWG (Flex)

Product Details

General

Application	For Terminations And Splices
Color	Clear
Material	PVC (polyvinyl chloride)
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810266175

Conductor Related

Conductor Range	#6 AWG to #4 AWG
-----------------	------------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)