



## HSC18T48PF

by Burndy  
Catalog ID: HSC18T48PF

Thin Wall Cross-Linked Clear Polyolefin Heat Shrink Tubing, #14-18 AWG, 600 V, Flame Retardant.

Features: Type HS-T-PF Is A Flexible Thin Wall, Flame Retardant Heat Shrink Tubing Made Of Crosslinked Polyolefin, The 2:1 Shrink Ratio Allows For Faster Shrink Recovery, Covering Wire Sizes 18 AWG To 300 KCMIL, Operating Temperatures From -55 To 135 DEG C With A Shrink Temperature Of 120 DEG C, Inner Diameter Expanded: 0.12 IN Minimum, Nominal Diameter: 1/8 IN, Conductor Range: 18 - 14 AWG, Material: Cross-Linked Polyolefin, Inner Diameter After Recovery: 06 IN Maximum

## Product Details

### General

Application	For Terminations And Splices
Color	Clear
Material	Polyolefin
Sub Brand	VISISHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810212387

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)