



KA25RK

by Burndy
Catalog ID: KA25RK

Prop 65 Notice

Copper Alloy Terminal, Conductor Range (Main/Primary): 4 - 1/0 AWG,
Bolt Size: 1/2 IN, Stud Size: 3/8 IN.

Features: Compact, Economical, High Copper Alloy Terminal For Joining
A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Stud Size:
3/8 IN, Length: 1-11/16 IN, Set Screw Type: Allen, Package: Clamshell,
Thickness: 3/23 IN, Hex Size: 1/2 IN, Width: 0.75 IN Pad, Height: 15/16 IN,
Installation Torque: 200 IN-LB

Product Details

General

Application	For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks
Hardware Type	1/2 UNF Socket/HexScrew
Installation Torque Recommended in-lb	200 LBS/in
Insulation	Y
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Temperature Rating	194
Trade Name	KA-LUG™
Type	Bolted Lugs & Terminals
UPC	781810359846
UPC 12 Digit	7818103598466

Dimensions

Dimension - B Length fraction	20/29 in
Dimension - B Length inch	0.69 in
Dimension - Height fraction	47/50 in
Dimension - Height inch	0.94 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - N inch	0.38 in
Dimension - Pad Width inch	0.75 in
Dimension - Stud Size inch	3/8

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	4 AWG-1/0

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	2

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)