



## KS28

by Burndy  
Catalog ID: KS28

Prop 65 Notice

Copper Split Bolt, Cu: 1-4/0 AWG (Run & Tap)

## Product Details

### General

Connector Type	Split Bolt
Installation Torque Recommended in-lb	650 in
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	SERVIT®
UPC	781810422007
UPC 12 Digit	7818104220077

### Dimensions

Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.46
Dimension - Width inch	1.17 in
Dimension - Width mm	30 mm
Width	1.18 in

### Conductor Related

Conductor - Copper Solid Run	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Run Range	1 AWG - 4/0 AWG
Conductor - Copper Solid Tap	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	1 AWG - 4/0 AWG
Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	1 STR - 4/0 STR
Conductor - Copper Str Tap	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	1 STR - 4/0 STR
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul>
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)