



## KA8CRK

by Burndy  
Catalog ID: KA8CRK

Prop 65 Notice

Copper Alloy Terminal, Bolt Size: 7/32 IN, Conductor Range (Main/Primary): 14 AWG Solid - 8 AWG Stranded, Installation Torque: 25 IN-LB.

Features: Compact, Economical, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Set Screw Type: Slot, Stud Size: #10, Width: 0.38 IN Pad, Installation Torque: 25 IN-LB, Hex Size: 7/32 IN, Length: 13/16 IN, Package: Clamshell, Dimension T: 3/32 IN, Height: 5/8 IN

## Product Details

### General

Application	For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks
Hardware Type	#12 UNC Slotted SetScrew
Installation Torque Recommended in-lb	25 LBS/in
Insulation	Y
Material	Copper
Material - Hardware	Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Temperature Rating	194
Trade Name	KA-LUG
Type	Bolted Lugs & Terminals
UPC	781810359914
UPC 12 Digit	7818103599144

### Dimensions

Dimension - B Length fraction	8/25 in
Dimension - B Length inch	0.32 in
Dimension - Height fraction	36/59 in
Dimension - Height inch	0.61 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.81 in
Dimension - N inch	0.19 in

Dimension - Pad Width inch	0.38 in
Dimension - Stud Size inch	#10
Dimension - Thread Size	-
Dimension - Width mm	0 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Solid Size Range	14 AWG-8 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	14 AWG-8 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	Y
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	5

## For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)