



## KA8C

by Burndy  
Catalog ID: KA8C

Prop 65 Notice

Copper Terminal, 1 Hole, 14 AWG (Sol)-8 AWG (Str), #10 Stud, 1 Screw.

Features: Compact, Economical, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks,  
Dimension T: 3/32 IN, Dimension N: 3/16 IN, Dimension K: 7/32 IN, Tongue Width: 3/8 IN, Installation Torque: 25 IN-LB, Length: 13/16 IN, Stud/bolt Hole Size: #10, Height: 5/8 IN

## Product Details

### General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks
Connector Type	Terminal
Hardware Type	#12
Material	Copper
Material - Hardware	Steel
Physical Attribute - Screw Type	Flat head round tip
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Type	Bolted Lugs & Terminals
UPC	781810362051

### Dimensions

Dimension - Height inch	15.42 in
Dimension - Hole Size fraction	7/32
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	20.6 mm
Dimension - Length Overall inch	0.81 in
Dimension - Mounting Hardware Bolt Size inch	12.24 UNC
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in
Dimension - Width inch	0.38 in
Dimension - Width mm	9.70 mm

### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	# 14 Sol. - # 8 Str.
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)