



KLU175TP

by Burndy
Catalog ID: KLU175TP

Prop 65 Notice

Cu Alloy Scrulug (Offset Pad Term Lug), #4-3/0 AWG (STR), 3/8 IN Stud, 2.20 IN L, Tin Plated, 1 IN Strip Length

Product Details

General

Connector Type	Terminal
Hardware Type	3/8 UNF Socket/HexScrew
Installation Torque Recommended in-lb	120
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810352700

Dimensions

Dimension - B Length fraction	22/31 in
Dimension - B Length inch	0.71 in
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.20 in
Dimension - N inch	0.43 in
Dimension - Pad Width inch	0.75 in
Dimension - Screw Size inch	3/8
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	4 AWG-3/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)