



KLU225TP

by Burndy
Catalog ID: KLU225TP

Cu Alloy Scrulug (Offset Pad Term Lug), #2-4/0 AWG (STR), 5/16 IN Stud, 2.55 IN L, Tin Plated, 1-5/16 IN Strip Length

Product Details

General

Connector Type	Terminal
Hardware Type	7/16 UNF Socket/HexScrew
Installation Torque Recommended in-lb	120
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810352755

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.55 in
Dimension - N inch	0.51 in
Dimension - Pad Width inch	0.99 in
Dimension - Screw Size inch	7/16
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	5/16

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)