



## KVS34

by Burndy  
Catalog ID: KVS34

Prop 65 Notice

Compact, two-piece, high strength, high copper alloy BURNDY OKLIP recommended for heavy duty connections. Neoprene rings hold DURIUM bolts in place during installation. Installed with ordinary wrench. Recommended tightening torque: 375 in-lb.

Features: Compact, Two-Piece, High Strength, High Copper Alloy BURNDY OKLIP Recommended For Heavy Duty Connections, Neoprene Rings Hold DURIUM Bolts In Place During Installation, Installed With Ordinary Wrench, Conductor Type: Run And Tap: Copperweld, Commercial Stranded Copper, Solid Copperweld, Installation Torque: 375 IN-LB, Conductor Spacer: No

## Product Details

### General

Application	For Copper, Copperweld
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVS, Compact
UPC	781810063200
UPC 12 Digit	7818100632000

### Dimensions

Dimension - Height inch	2.65 in
Dimension - Stud Size inch	1/2 in
Dimension - Width inch	2.20 in

### Conductor Related

Conductor - Copper Str Run Range	400 kcmil - 500 kcmil
Conductor - Copper Str Tap Range	10 str. - 500 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Solid-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C

Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)