



KVS44

by Burndy
Catalog ID: KVS44

Prop 65 Notice

Compact, two-piece, high strength, high copper alloy BURNDY OKLIP recommended for heavy duty connections. Neoprene rings hold DURUM bolts in place during installation. Installed with ordinary wrench, wrench size: 15/16 cross flats.

Features: Compact, Two-Piece, High Strength, High Copper Alloy BURNDY OKLIP Recommended For Heavy Duty Connections, Neoprene Rings Hold DURUM Bolts In Place During Installation, Installed With Ordinary Wrench, Conductor Type: Run: Commercial Stranded Copper, Tap: Commercial Stranded Copper, Installation Torque: 500 IN-LB, Conductor Spacer: No

Product Details

General

Application	For Copper And Copperweld, Heavy Duty Connections
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVS
UPC	781810064603
UPC 12 Digit	7818100646033

Dimensions

Dimension - Height inch	3.71 in
Dimension - Stud Size inch	5/8 in
Dimension - Width inch	3.03 in

Conductor Related

Conductor - Copper Str Run Range	500 kcmil- 1000 kcmil
Conductor - Copper Str Tap Range	3/0 str.- 1000 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap • CU Weld C Solid-Run • CU Weld C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)