



KPA28UNPL

by Burndy
Catalog ID: KPA28UNPL

Prop 65 Notice

Copper Alloy Scrulug, 1/0 Str. - 4/0 Str., 2.29 in L, .97 in W.

Features: High Copper Alloy Unplated Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Especially Good In Light Industrial Applications, The Tongue And Body Are A One-Piece Design, The Pressure Bar Equalizes Pressure Over The Conductor And Prevents The Screw From Cutting Into The Cable, Dimension T: 0.13 IN, Dimension C: 0.97 IN, Dimension N: 0.53 IN, Dimension K: 0.4 IN, Length: 2.29 IN, Installation Torque: 250 IN-LB, Stud/bolt Hole Size: 3/8 IN, Dimension D: 1.12 IN, Height: 1.66 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks
Connector Type	Terminal
Installation Torque Recommended in-lb	250
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810144497

Dimensions

Dimension - D inch	1.12 in
Dimension - Height fraction	1-21/32 in
Dimension - Height inch	1.66 in
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	61 mm
Dimension - Length Overall inch	2.40 in
Dimension - N inch	0.53 in
Dimension - Pad Width inch	0.97 in
Dimension - Stud Size fraction	3/8 in
Dimension - Stud Size inch	0.375 in

Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy;150 (61) Navy
Conductor - Copper Str Navy Size Range	125 (61) Navy-150 (61) Navy
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1/0 -4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Navy-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)