



KPA4CTPG2

by Burndy
Catalog ID: KPA4CTPG2

Prop 65 Notice

Copper Alloy Scrulug, 14 - 6 AWG, 1.28 in L, .50 in W, Tin Plated

Product Details

General

Connector Type	Terminal
Hardware Type	5/16 Dia.Slot Robertson
Installation Torque Recommended in-lb	45 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810076972

Dimensions

Dimension - D inch	0.71 in
Dimension - Height fraction	1 in
Dimension - Height inch	1.00 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.28 in
Dimension - N inch	0.33 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	14 AWG-6 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	14 AWG-6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)