



KPA8CUPRK

by Burndy
Catalog ID: KPA8CUPRK

Prop 65 Notice

Copper Alloy Scrulug Terminal, Conductor Range (Main/Primary): 14 AWG Solid - 6 AWG Stranded, Installation Torque: 35 IN-LB.

Features: High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Plain Copper Finish, One Piece Design, Superior Torque And Pull Out Performance, Convenient Range Taking Design, Reduces Catalog Numbers, One Catalog Number Accommodates several Conductor Sizes, High Conductivity Copper Alloy, Long Lasting, Reliable Contact, Compact Design, Easy To Use, Slot Robertson Screw, Hex Head, Hex Socket Bolt, No Special Installation Tools Required, Eliminates Over-Torquing/Potential Conductor Damage, Width: 0.38 IN Pad, Thickness: 07 IN, Installation Torque: 35 IN-LB, Stud Size: #10, Height: 0.81 IN, Number Of Screws: 1, Dimension N: 0.24 IN, Package: Clamshell, Wire Strip Length: 15/32 IN, Length: 11 IN, Dimension D: 0.51 IN, Set Screw Type: Slot Robertson

Product Details

General

Application	For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks
Hardware Type	1/4 Dia.Slot Robertson
Installation Torque Recommended in-lb	35 LBS/in
Insulation	Y
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Temperature Rating	194
Trade Name	SCRULUG
Type	Bolted Lugs & Terminals
UPC	781810359969
UPC 12 Digit	7818103599699

Dimensions

Dimension - D inch	0.56 in
Dimension - Height fraction	64/79 in
Dimension - Height inch	0.81 in
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.04 in

Dimension - N inch	0.22 in
Dimension - Pad Width inch	0.38 in
Dimension - Strip Length inch	15/32
Dimension - Stud Size inch	#10
Dimension - Thread Size	-
Dimension - Width mm	0 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	14 AWG-6 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	14 AWG-6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	5

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)