

NA12

by Burndy
Catalog ID: NA12

Substation Connectors



Product Details

General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	1
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1 hole
Plated	Y
Plating Type	Bright Dipped
UPC	621945100923
UPC 12 Digit	6219451009233

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height inch	1.50 in
Dimension - Hole Size fraction	7/16
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.50 in
Dimension - Width inch	2.13 in
Dimension - Width mm	54 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	3/8 IPS
Conductor - Copper Tube Std Size Range	3/8 IPS

Conductor Type	<ul style="list-style-type: none">• CU Tube Std-Size• CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)