

# NA142N

by Burndy  
Catalog ID: NA142N

Prop 65 Notice

Copper Bolted Terminal , Tube to Flat , 3/4" Cu Pipe , 2 Pad Holes , 230 kV.



## Product Details

### General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1.63 x 3 - 2 holes
Plated	N
Plating Type	Unplated
UPC	781810002322
UPC 12 Digit	7818100023222

### Dimensions

Dimension - B Length inch	2.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2
Dimension - Height inch	2.00 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.25 in
Dimension - N inch	0.625 in
Dimension - Pad Width inch	1.63 in
Dimension - Width inch	2.44 in
Dimension - Width mm	62 mm

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube EH Size	3/4 IPS
Conductor - Copper Tube EH Size Range	3/4 IPS
Conductor - Copper Tube Std Size	3/4 IPS
Conductor - Copper Tube Std Size Range	3/4 IPS
Conductor Type	<ul style="list-style-type: none"> <li>• CU Tube Std-Size</li> <li>• CU Tube EH-Size</li> </ul>
Number Of Conductors	1

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)