



KS203

by Burndy
Catalog ID: KS203

Prop 65 Notice

Copper Split Bolt, Cu: 8 AWG (Str)-4 AWG (Sol) (Run & Tap).

Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Type KS-3 Accommodates 3 Maximum Size Conductors, Conductor Type: Run: Solid Copperweld, Commercial Stranded and Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld, Tap: Solid Copperweld, Commercial Stranded and Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld, Installation Torque: 165 IN-LB, Servit Cover: SC2

Product Details

General

Application	For Copper, Copperweld, Direct Burial Cables
Connector Type	Split Bolt
Installation Torque Recommended in-lb	165 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS-3
UPC	781810022009
UPC 12 Digit	7818100220099

Dimensions

Dimension - Cross Flats inch	.68 in
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.2
Dimension - Width inch	0.78 in
Dimension - Width mm	20 mm
Width	0.51 in

Conductor Related

Conductor - Copper Solid Run	4 AWG
Conductor - Copper Solid Run Range	4 AWG
Conductor - Copper Solid Tap	4 AWG
Conductor - Copper Str Run	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Run Range	8 STR - 4 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG

Conductor - Copper Str Tap Range	8 STR - 4 STR
Conductor - CopperWeld Solid Run	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - CopperWeld Solid Run Range	10 AWG-4 AWG
Conductor - CopperWeld Solid Tap	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - CopperWeld Solid Tap Range	10 AWG-4 AWG
Conductor - CopperWeld Str Run	8 D AWG;7 A AWG;7 D AWG;6 A AWG
Conductor - CopperWeld Str Run Range	8 D AWG-6 A AWG
Conductor - CopperWeld Str Tap	8 D AWG;7 A AWG;7 D AWG;6 A AWG
Conductor - CopperWeld Str Tap Range	8 D AWG-6 A AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)