

NA154N90

by Burndy
Catalog ID: NA154N90

Prop 65 Notice

Substation Connectors



Product Details

General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
UPC	781810030752
UPC 12 Digit	7818100307522

Dimensions

Dimension - B Length inch	2.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	2.56 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.21 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	2.75 in
Dimension - Width mm	70 mm
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube Std Size Range	1 IPS
Conductor Type	<ul style="list-style-type: none">• CU Tube Std-Size• CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)