



NA1744NHQ

by Burndy
Catalog ID: NA1744NHQ

Prop 65 Notice

Substation Connectors

Product Details

General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	4 x 4 - 4 holes
Plated	N
Plating Type	Unplated
UPC	781810456880
UPC 12 Digit	7818104568800

Dimensions

Dimension - B Length inch	2.69 in
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	3.09 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.07 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	3.82 in
Dimension - Width mm	97 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	1 1/2 IPS
Conductor - Copper Tube Std Size Range	1 1/2 IPS
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)