



## KVS40

by Burndy  
Catalog ID: KVS40

Prop 65 Notice

Compact, two-piece, high strength, high copper alloy BURNDY OKLIP recommended for heavy duty connections. Neoprene rings hold DURUM bolts in place during installation. Installed with ordinary wrench. Recommended tightening torque: 500 in-lb.

Features: Compact, Two-Piece, High Strength, High Copper Alloy BURNDY OKLIP Recommended For Heavy Duty Connections, Neoprene Rings Hold DURUM Bolts In Place During Installation, Installed With Ordinary Wrench, Installation Torque: 500 IN-LB, Conductor Type: Run: Copperweld, Commercial Stranded Copper, Tap: Copperweld, Commercial Stranded Copper, Conductor Spacer: No

## Product Details

### General

Application	For Copper And Copperweld, Heavy Duty Connections
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVS
UPC	781810063903
UPC 12 Digit	7818100639033

### Dimensions

Dimension - Height inch	3.19 in
Dimension - Stud Size inch	1/2 in
Dimension - Width inch	2.50 in

### Conductor Related

Conductor - Copper Str Run Range	400 - 800 kcmil
Conductor - Copper Str Tap Range	3/0 str. - 800 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Solid-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)