

# NA17ACG3

by Burndy  
Catalog ID: NA17ACG3

Prop 65 Notice

Substation Connectors



## Product Details

### General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Aluminum
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	621945249516
UPC 12 Digit	6219452495166

### Dimensions

Dimension - B Length inch	4.00 in
Dimension - D inch	3.75 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	3.88 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.88 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	3.66 in
Dimension - Width mm	93 mm
Length	8.13 in

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - AL Tube Std Size	1 1/2 IPS
Conductor - AL Tube Std Size Range	1 1/2 IPS

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	11/2 IPS IPS
Conductor - Copper Tube Std Size Range	11/2 IPS IPS
Conductor Type	<ul style="list-style-type: none"> <li>• AL Tube Std-Size</li> <li>• CU Tube Std-Size</li> </ul>
Number Of Conductors	1

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)