

NA18A4N45Q

by Burndy
Catalog ID: NA18A4N45Q

Substation Connectors



Product Details

General

Application	Substation
Connector Type	Terminal
Material	Aluminum Alloy
Material - Hardware	Aluminum
Physical Attribute - Pad Orientation	45 Degree
Plated	N
Plating Type	Unplated
UPC	781810247594
UPC 12 Digit	7818102475944

Dimensions

Dimension - B Length inch	4.25 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	4.47 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.35 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	4.50 in
Dimension - Width mm	114 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube Std Size	2 IPS
Conductor - AL Tube Std Size Range	2 IPS
Conductor - Copper Tube Std Size	2 IPS IPS
Conductor - Copper Tube Std Size Range	2 IPS IPS

Conductor Type	<ul style="list-style-type: none">• AL Tube Std-Size• CU Tube Std-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)