



NA154N

by Burndy
Catalog ID: NA154N

Prop 65 Notice

Copper Bolted Terminal , Tube to Flat , 1" Cu Pipe , 4 Pad Holes , 230 kV.

Product Details

General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Plated	N
Plating Type	Unplated
UPC	781810002445
UPC 12 Digit	7818100024455

Dimensions

Dimension - B Length inch	2.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2-1/8
Dimension - Height inch	2.06 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.25 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	2.75 in
Dimension - Width mm	70 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube EH Size	1 IPS
Conductor - Copper Tube EH Size Range	1 IPS
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube Std Size Range	1 IPS
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)