

NA22A4NU

by Burndy
Catalog ID: NA22A4NU

Prop 65 Notice

Substation Connectors



Product Details

General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	480 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	5.26 x 3 - 0 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	781810119396
UPC 12 Digit	7818101193966

Dimensions

Dimension - B Length inch	6.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.94 in
Dimension - Height inch	6.22 in
Dimension - L Length Overall mm	236 mm
Dimension - Length Overall inch	9.31 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	5.25 in
Dimension - Width inch	6.62 in
Dimension - Width mm	168 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube Std Size	4 IPS
Conductor - AL Tube Std Size Range	4 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	4 IPS IPS
Conductor - Copper Tube Std Size Range	4 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)