

NA17A4N

by Burndy
Catalog ID: NA17A4N

Prop 65 Notice

Al Terminal, 1.75" Spacing, Bolted, Tube to Flat, 1-1/2" IPS, 1.90" Dia, 4 NEMA Pad Holes



Product Details

General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Plated	N
Plating Type	Unplated
UPC	781810003749
UPC 12 Digit	7818100037499

Dimensions

Dimension - B Length fraction	4 in
Dimension - B Length inch	4.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	1.76 in
Dimension - Height fraction	3-7/8
Dimension - Height inch	3.88 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	191 mm
Dimension - Length Overall inch	7.50 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.00 in
Dimension - Width fraction	3-11/16 in
Dimension - Width inch	3.64 in
Dimension - Width mm	92 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube Std Size	1 1/2 IPS
Conductor - AL Tube Std Size Range	1 1/2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	1 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	1 1/2 IPS IPS
Conductor Type	<ul style="list-style-type: none">• AL Tube Std-Size• CU Tube Std-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)