

## NHNT2229

by Burndy  
Catalog ID: NHNT2229

Prop 65 Notice

Substation Connectors



## Product Details

### General

Application	Substation
Connector Type	T-Connector
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Type	Tube to Cable Couplers
UPC	781810219676
UPC 12 Digit	7818102196766

### Dimensions

Dimension - B Length inch	3.25 in
Dimension - Height inch	4.26 in
Dimension - L Length Overall mm	264 mm
Dimension - Length BB inch	2.63 in
Dimension - Length Overall inch	10.38 in
Dimension - Width inch	2.50 in
Dimension - Width mm	64 mm

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - Connection Combination	Tube to Cable
Conductor - Copper Solid Tap	5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	5 AWG-4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil

Conductor - Copper Str Tap Range	6 AWG-250 kcmil
Conductor - Copper Tube Std Run	4 IPS
Conductor - Copper Tube Std Run Range	4 IPS
Conductor Type	<ul style="list-style-type: none"> <li>• CU Tube Std-Run</li> <li>• CU C Str-Run</li> <li>• CU C Solid-Run</li> <li>• CU C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)