



# PENE8

by Burndy  
Catalog ID: PENE8

Oxide Inhibiting Electrical Joint Compound, 8 OZ, For Cu-Cu, Cu Conduit Threads & Grounding Applications.

consists of a non-petroleum base vehicle in which copper granules are suspended, UL Listed to 600 volts

## Product Details

### General

|   |                               |
|---|-------------------------------|
| Application                             | Copper to copper applications |
| Application - For Use On                | Copper to Copper              |
| Container Type                          | Squeeze Bottle                |
| Pour Point                              | -40 °F                        |
| Sub Brand                               | PENETROX                      |
| Temperature - Dropping Point Fahrenheit | 350 °F                        |
| Trade Name                              | PENETROX™                     |
| Type                                    | Sealing compound              |
| UPC                                     | 781810592854                  |
| UPC 12 Digit                            | 7818105928544                 |
| Viscosity at 100 Fahrenheit             | 250 °F                        |

### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

### Logistics

|                       |      |
|-----------------------|------|
| Container Size        | 8 oz |
| Minimum Pack Quantity | 1    |

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)