



PENA1/2

by Burndy
Catalog ID: PENA1/2

Oxide Inhibiting Electrical Joint Compound, 1/2 OZ, For Al-Al, Al-Cu & Al Conduit Threads.

Features: PENETROX A Consists Of A Natural (Petro - Leum) Base Vehicle In Which Zinc Particles Are Suspended, For Aluminum To Aluminum, Aluminum To Copper Applications And Aluminum Conduit Threads, It Is Not Recommended For Use With Rubber And Polyethylene Insulated Conductors, UL Listed To 600 Volts, Dropping Point (minimum): 230 DEG F, Pour Point(maximum): -15 DEG F, Penetration (unworked): 230 In Accordance To ASTM D217, Container Consist Of: Natural (Petroleum) Base Vehicle With Zinc Particles Suspended, Voltage Rating: 600 V

Product Details

General

Application	For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit
Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Tube
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	A
UPC	781810592601
UPC 12 Digit	7818105926011
Viscosity at 100 Fahrenheit	305 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	1/2 oz
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)

