



PENEQT

by Burndy
Catalog ID: PENEQT

Oxide Inhibiting Electrical Joint Compound, 1 Quart, For Cu-Cu, Cu Conduit Threads & Grounding Applications.

Features: PENETROX E Consists Of A Non-Petroleum Base Vehicle In Which Copper Granules Are Suspended, Recommended For Copper To Copper Applications, Grounding And For Use On Copper Conduit Threads, UL Listed, Pour Point(maximum): -10 DEG F, Dropping Point (minimum): 500 DEG F, Penetration (unworked): 250 In Accordance To ASTM D217, Container Consist Of: Non - Petroleum Base Vehicle In Which Copper Granules Are Suspended

Product Details

General

Application	For Copper To Copper
Application - For Use On	Copper to Copper
Container Type	Tub
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	E
UPC	781810592946
UPC 12 Digit	7818105929466
Viscosity at 100 Fahrenheit	250 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	1 Quart
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)