



PENAQT

by Burndy
Catalog ID: PENAQT

Oxide Inhibiting Electrical Joint Compound, 1 Quart, For Al-Al, Al-Cu & Al Conduit Threads.

Features: PENETROX A Consists Of A Natural (Petro - Leum) Base Vehicle In Which Zinc Particles Are Suspended, For Aluminum To Aluminum, Aluminum To Copper Applications And Aluminum Conduit Threads, It Is Not Recommended For Use With Rubber And Polyethylene Insulated Conductors, UL Listed To 600 Volts, Container Consist Of: Natural (Petroleum) Base Vehicle With Zinc Particles Suspended, Pour Point(maximum): -15 DEG F, Dropping Point (minimum): 230 DEG F, Penetration (unworked): 230 In Accordance To ASTM D217, Voltage Rating: 600 V

Product Details

General

| | |
|---|---|
| Application | For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit |
| Application - For Use On | Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper |
| Container Type | Tub |
| Pour Point | -15 °F |
| Sub Brand | PENETROX |
| Temperature - Dropping Point Fahrenheit | 230 °F |
| Trade Name | PENETROX™ |
| Type | A |
| UPC | 781810592908 |
| UPC 12 Digit | 7818105929088 |
| Viscosity at 100 Fahrenheit | 305 °F |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---------|
| Container Size | 1 Quart |
| Minimum Pack Quantity | 1 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)

